



External micrometer, Measuring range: 0-25mm



Order data

Order number	420450 0-25
GTIN	7630041104080
Item class	45A

Description

Version:

Precision lapped, carbide-tipped measuring faces.

Hardened and ground measuring spindle.

Locking by clamping lever.

With ratchet and hand temperature protection.

With clearly engraved, black divisions and numerals.

Supplied with:

External micrometer without setting dimension.

Technical description

Spindle Ø	6.5 mm
Scale divisions	0.01 mm
Measuring range	0 - 25 mm
Barrel Ø	18.5 mm
Micrometer barrel graduations	1/50 mm
Calibration	B1
Error limit	2 µm
Standard	DIN 863
Measurement technology	analogue

Packaging	sturdy box
Type of product	External tube micrometer

Services

DAkkS calibration External micrometer without setting dimension maximum measuring range 100 mm	022010 100
Calibration External micrometer without setting dimension maximum measuring range 25 mm	022000 25