



External micrometer, Measuring range: 50-75mm



Order data

Order number	420450 50-75
GTIN	7630041104103
Item class	45A

Description

Version:

Precision lapped, carbide-tipped measuring faces.

Hardened and ground measuring spindle.

Locking by clamping lever.

With ratchet and hand temperature protection.

With clearly engraved, black divisions and numerals.

Supplied with:

External micrometer without setting dimension.

Technical description

Barrel Ø	18.5 mm
Micrometer barrel graduations	1/50 mm
Scale divisions	0.01 mm
Measuring range	50 - 75 mm
Spindle Ø	6.5 mm
Calibration	B1
Error limit	2 µm
Standard	DIN 863
Measurement technology	analogue

Packaging	sturdy box
Type of product	External tube micrometer

Services

DAkkS calibration External micrometer without setting dimension maximum measuring range 100 mm	022010 100
Calibration External micrometer without setting dimension maximum measuring range 100 mm	022000 100

Accessories

Micrometer setting standard overall length 50 mm	421100 50
--	-----------