



## External micrometer, Measuring range: 75-100mm



### Order data

Order number	420450 75-100
GTIN	7630041104110
Item class	45A

### Description

#### Version:

#### Precision lapped, carbide-tipped measuring faces.

Hardened and ground measuring spindle.

Locking by clamping lever.

With ratchet and hand temperature protection.

With clearly engraved, black divisions and numerals.

#### Supplied with:

External micrometer without setting dimension.

### Technical description

Spindle Ø	6.5 mm
Barrel Ø	18.5 mm
Micrometer barrel graduations	1/50 mm
Measuring range	75 - 100 mm
Scale divisions	0.01 mm
Calibration	B1
Error limit	3 µm
Standard	DIN 863
Measurement technology	analogue

Packaging	sturdy box
Type of product	External tube micrometer

### Services

DAkkS calibration External micrometer without setting dimension maximum measuring range 100 mm	022010 100
Calibration External micrometer without setting dimension maximum measuring range 100 mm	022000 100

### Accessories

Micrometer setting standard overall length 75 mm	421100 75
--	-----------