

 steinel**Heat gun, Type: 008338****Order data**

Order number	078321 008338
GTIN	4007841008338
Item class	07E

Description**Version:**

Electronically controlled heat gun with stepless regulation of the air quantity.
High-quality straight handle heat gun HG 2620 E for professional applications.

- **Connecting cable can be easily exchanged.**
- **Exchangeable ceramic heater with a service life of approx. 800 h.**
- **Air pressure of up to 4,000 Pa.**
- **Temperature can be set from 50 – 700°C using a joystick.**
- **Air volume controlled from 150 – 500 l/min.**
- **Safeguard against accidental restart.**
- **Cooling stage.**
- **LCD display and residual-heat indicator.**

Application:

For welding and forming plastics, for shrinking, removing paints, soldering, drying, and thawing.

Technical description

Power consumption	2300 W
Air temperature	50 - 700 °C
Weight	840 g
Manufacturer's designation	HG 2620E
Air flow volume	150 - 500 l/min
Power supply	Mains operated

Type of product

Hot air pistol

Accessories

Temperature scanner HL Scan Type 014919	078326 014919
Temperature scanner HG Scan PRO Type 007553	078325 007553
Temperature scanner HG Scan PRO Type 007690	078325 007690
Heat gun accessory set 12 pieces Type 075569	078329 075569