



Pneumatic-hydraulic pop rivet nut setting tool FireFox®, Type: 1



Order data

Order number	770515 1
GTIN	4007081920841
Item class	74A

Description

Version:

Operating pressure 5 – 7 bar. Automatic nut spinning procedure as soon as the pop rivet nut is gently pressed on to the threaded pin. Extremely productive operation due to quick spinning and lightning-fast setting process.

Supplied with:

Two assembly wrenches 24 / 27 AF, 1 hexagon bit driver 4 AF, 1 bottle of hydraulic oil 100 ml, 1 oil refill container. Nozzle and threaded mandrel M3, M4, M5, M6.

Note:

Spare nozzles are available under No. 770516. For pop rivet nuts from M3 to M6 of all materials apart from M6 stainless steel.

Technical description

Stroke	7.5 mm
Weight	1.96 kg
Air consumption per setting operation (depending on the thread)	max. 2 l

Hose connection	6 mm
for pop rivet nuts steel/alu	M3 – M6
Setting force selectable, max. at 5 bar	12000 N
for pop rivet nuts in all materials	M3 – M6
Hose connection	1/4 in
Type of product	Pop riveter

Accessories

Spare nozzle with threaded spigot Type M3	770516 M3
Spare nozzle with threaded spigot Type M5	770516 M5
Spare nozzle with threaded spigot Type M4	770516 M4
Spare nozzle with threaded spigot Type M6	770516 M6