

Garant**Light metal spirit level, Length: 600mm****Order data**

Order number	467020 600
GTIN	4045197720504
Item class	41H

Description**Version:**

Thick-walled anodised aluminium profile with very high rigidity. Flat and Vee-form measuring faces for perfect alignment on surfaces, pipes and edges. Flush horizontal vial with magnifying effect creates distortion-free view of the vial bubble.

Version of the advertising text:

Thick-walled anodised aluminium profile with very high rigidity. Flat and Vee-form measuring faces for perfect alignment on surfaces, pipes and edges. Flush horizontal vial with magnifying effect creates distortion-free view of the vial bubble. **Error limit for measurement reversal: 0.75 mm/m.**

Technical description

Length	600 mm
Error limit in normal position	0.5 mm/m
Error limit for overhead measurement	0.75 mm/m
Cross section	24 × 55 mm
Type of product	Spirit level