

**Garant****Granite plate Accuracy class 0, Length×Width: 1000X630mm****Order data**

Order number	430190 1000X630
GTIN	4045197720603
Item class	41C

**Description****Version:**

Specially selected natural granite.

- **Free from defects, homogeneous structure.**
- **Resistant to deflection and to warping.**
- **Absolutely rust-proof and acid resistant, low thermal conductivity.**
- **Micro-fine machine surface (diamond lapped). Within all the permissible tolerances.**
- **Ground outside edges, visually true.**
- **For static determination of position, contact points (steel ball inserts) are fitted to the underside.**
- **Harder than hardened steel (Mohs hardness scale 6 – 7), non-magnetic and electrically non-conductive.**

**Accuracy:**

Final manufacturing and inspection take place in computer-controlled climatic rooms. The used measuring equipment guarantees the exact connection to national and international calibration laboratories.

**DIN 876/0 – Precision diamond lapped** for inspection.

**Supplied with:**

**Supplied with test certificate, transport packing.** Including steel ball inserts.

**Note:**

**On request:** Stainless steel screw inserts, steel T-slot rails (steel T-slot rails not available for No. 430190), accuracy 000, other sizes, intermediate sizes. Delivery excluded.

**Technical description**

Flatness	0.008 mm
Thickness	100 mm

Weight	189 kg
Number of steel ball inserts	3
Standard	DIN 876
Accuracy	0 mm
Test certificate	Manufacturer's test certificate
Type of product	Graduated plate

---

## Accessories

Cleaner for natural granite Contents 0,5 l	431841 0,5
Care product for granite Contents 0,5 l	431840 0,5
Support cabinet for insert size length×width 1000X630 mm	431050 1000X630