

Garant

Support frame, for insert size length×width: 1500X1000mm



Order data

Order number	431000 1500X1000
GTIN	4045197720658
Item class	41C

Description

Version:

Sturdy welded construction including levelling fittings. Uneven floors can be compensated using height compensation screws..

Support frame, steel sections, paint finish RAL 9006 white aluminium. Beech ply storage shelf.

Application:

The natural granite tables No. 430190 - 430500 are mounted on pre-determined points (steel ball inserts).

- **For plates up to 630×630 mm. For setting up on workbenches and the like, adjustable screw jacks No. 373500 are most suitable.**
- **The support jacks are adjustable for height and allows the table to be levelled (3-point contact and 2 support screws as protection against tipping)**

Note:

For vibration-absorbing machine mounts, please order 4× No. 086002 size 850.

Height adjustment: 25 mm

Support cabinet height: 720 mm

Support cabinet width: 1060 mm

Support cabinet depth: 830 mm

Height of support cabinet incl. bearing sets: 780 mm

Load capacity, distributed: 2000 kg

Weight: 50 kg

Technical description

Weight	50 kg
Support cabinet height	720 mm
suitable for worktop size lengthxwidth	1500x1000 mm
Support cabinet width	1060 mm
Load capacity, distributed	2000 kg
Support cabinet depth	830 mm
Material of storage shelf	Beech ply
maximum working height (top face of the granite table)	900 mm
Height of support cabinet incl. bearing sets	780 mm
Height adjustment	25 mm
Type of product	Sub-frame