



MS polymer adhesive and sealant Multiflex, 290 ml, Colour: WHITE



Order data

Order number	083482 WHITE
GTIN	4260205360187
Item class	08G

Description

Version:

High quality **1-component adhesive and sealant compound, based on MS polymer**, weather-resistant and UV-resistant. Even adheres to moist substrates, permanently resilient, quick curing even at low temperatures. Easy to work, can be painted over.

Colour: white

Technical description

Manufacturer's designation	Multiflex
Colour	white
Stretch capability	250 %
Suitable for application area	Assembly
Characteristics	UV-resistant
Characteristics	weatherproof
Characteristics	colour-fast
Characteristics	can be painted over

Characteristics	resistant to ageing
Characteristics	Silicone-free
Capacity	290 ml
Shape	paste
Suitable for material	wood
Suitable for material	Plastic
Suitable for material	Concrete
Suitable for material	Glass
Suitable for material	Aluminium
Suitable for material	Metal
Suitable for material	Steel
Chemical basis	MS polymer
Working life after date of manufacture	12 mo
Processing temperature	5 - 40 °C
Functional strength to	1440 min
Storage temperature	5 - 25 °C
Kinematic viscosity	21 mm ² /s
Touch dry after	10 min
Flashpoint	60 °C
Hardness according to Shore A	60
Density	1.54 g/cm ³
Operating temperature range	-40 - 90 °C
Product name attribute	290 ml
Type of product	Sealing compound

Accessories

Cartridge gun 12:1 Type	083501
Cartridge gun	083500

Compressed-air cartridge gun	083507
Fully enclosed cartridge gun assortment, 4 pieces Type	083502