Garant

Support cabinet, for insert size length×width: 2000X1000 mm



Order data

Order number	431050 2000X1000
GTIN	4045197720702
Item class	41C

Description

Version:

Sturdy welded construction including levelling fittings. Uneven floors can be compensated using height compensation screws.

Support cabinet, casing made from sheet steel, with swing-door (including storage shelf) and/ or drawers depending on size, including GARANT locking system. Paint finish of the shell RAL 9006 aluminium white, front faces RAL 5011 steel blue.

Application:

The natural granite tables No. 430190 - 430500 are mounted on pre-determined points (steel ball inserts).

- For plates up to 630×630 mm. For setting up on workbenches and the like, adjustable screw jacks No. 373500 are most suitable.
- The support jacks are adjustable for height and allows the table to be levelled (3-point contact and 2 support screws as protection against tipping)

Fitted with:

Drawer front height (centre): 60; 100; 120; 200 mm Door height (left): 480 mm

Door height (right): 480 mm

Note:

For vibration-absorbing machine mounts, please order 4× No. 086002 size 850.

Cylinder lock: modular barrel

Support cabinet height: 720 mm

Support cabinet width: 1566 mm

Data sheet

Support cabinet depth: 780 mm Height of support cabinet incl. bearing sets: 780 mm Drawer usable width: 490 mm Drawer usable depth: 520 mm

Technical description

Support cabinet height	720 mm
Electronic locking system can be retrofitted	yes
Support cabinet width	1566 mm
Drawer usable depth	520 mm
Support cabinet depth	780 mm
Weight	154 kg
suitable for worktop size length×width	2000×1000 mm
Number of drawers	4
Drawer usable width	490 mm
Number of doors	2
Load capacity, distributed	2000 kg
maximum working height (top face of the granite table)	900 mm
Height of support cabinet incl. bearing sets	780 mm
Drawer/pull-out shelf load capacity	100 kg
Drawer runner extension (partial/full extension)	90 %
Height adjustment	25 mm
Hoffmann perforated panel grid interval	9×9
Cylinder lock	modular barrel
Type of product	Base cabinet for measurement technology