

Garant GRIDLINE

Support leg, Height: 800mm**Order data**

Order number	927000 800
GTIN	4062406107291
Item class	9GG

Description**Version:**

Of steel hollow section, 50 mm wide with cross bracing and mounting for height adjustment at 25 mm intervals. Feet with plastic pads, do not damage the floor. With cable slots - for simple and professional routing of media cables / power cables.

Colour:

Light grey RAL 7035, **powder-coated**.

Note:

Support legs without rear panel or cupboards require stabilising plates No. 927122 for stiffening. The height is to the underside of the worktop. Pre-assembled workbenches must be secured against tipping.

Technical description

Depth	700 mm
Height	800 mm
suitable for worktop depth	750 mm
Width	50 mm

Weight	6.9 kg
Design version	Steel hollow section construction
Material thickness	1.5 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Support leg

Accessories

Floor pads, set, 2 pieces Type 2	927092 2
Height adjustment for GridLine workbenches Type M12	927090 M12