

Garant GRIDLINE

**Support leg, Height: 900mm****Order data**

Order number	927000 900
GTIN	4062406107307
Item class	9GG

**Description****Version:**

Of steel hollow section, 50 mm wide with cross bracing and mounting for height adjustment at 25 mm intervals. Feet with plastic pads, do not damage the floor. With cable slots - for simple and professional routing of media cables / power cables.

**Colour:**

Light grey RAL 7035, **powder-coated**.

**Note:**

Support legs without rear panel or cupboards require stabilising plates No. 927122 for stiffening. The height is to the underside of the worktop. Pre-assembled workbenches must be secured against tipping.

**Technical description**

Height	900 mm
Width	50 mm
Depth	700 mm
suitable for worktop depth	750 mm

Weight	7.6 kg
Design version	Steel hollow section construction
Material thickness	1.5 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Support leg

---

## Accessories

Height adjustment for GridLine workbenches Type M12	927090 M12
Floor pads, set, 2 pieces Type 2	927092 2