



## Plain arbor for screw-in milling cutters, $\varnothing d = 32$ mm, Thread M $\times$ Length L2: M12X134



### Order data

Order number	301357 M12X134
GTIN	4062406107499
Item class	32A

### Description

#### Version:

Shank tolerance h6.

#### Application:

For mounting shrink-fit chucks.

### Technical description

L <sub>2</sub>	59.5 mm
Reach L <sub>1</sub>	134 mm
Bore $\varnothing D_1$	12.5 mm
$\varnothing D_2$	21 mm
Overall length L	300 mm
Adapter	$\varnothing d = 32$ mm
Through-coolant	yes
Type of product	Threaded copy mill arbor