


Garant
VARIO-LINE toolholder, left-hand, Shank height h: 25mm

Order data

Order number	273795 25
GTIN	4045197721334
Item class	21W

Description
Suitable for :

Blade carrier No. 273799.

Supplied with:

Including assembly screws.

Note:
 $L = L_1 + L_3$ (blade carrier).

 Functional width L_4 : 30 mm

 L_1 : 150 mm

 L_2 : 24.5 mm

Screw: 279815 9 (TX25; 6.0 Nm)

Technical description

Shank height h	25 mm
L_2	24.5 mm
Functional width L_4	30 mm
Screw	279815 9 (TX25; 6.0 Nm)
L_1	150 mm
Application type	left-hand
Type of product	Clamping toolholder

Accessories

Clamping screw Type 9	279815 9
PrecisionBit for Torx®, shank E 6.3 Torx® profile TX10	674248 TX10
Clamping screw	279910
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500