

Garant GRIDLINE

**Support leg including manual height adjustment, Height: 800mm****Order data**

Order number	927001 800
GTIN	4062406107642
Item class	9GG

**Description****Version:**

Of steel hollow section, 50 mm wide with cross bracing and mounting for height adjustment at 25 mm intervals. Feet with plastic pads, do not damage the floor. With cable slots - for simple and professional routing of media cables / power cables.

**Height adjustment 150 mm.****Supplied with:**

Support leg with manual height adjustment No. 927080 size 150.

**Colour:**

Light grey RAL 7035, **powder-coated.**

**Note:**

Support legs without rear panel or cupboards require stabilising plates No. 927122 for stiffening. The height is to the underside of the worktop.

Pre-assembled workbenches must be secured against tipping.

**Technical description**

Height adjustment interval	25 mm
Width	50 mm

Depth	700 mm
suitable for worktop depth	750 mm
Height adjustment range	800 - 950 mm
Design version	Steel hollow section construction
Material thickness	1.5 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Support leg

---

## Accessories

Manual height adjustment Type M10	927091 M10
Manual height adjustment Height adjustment 150 mm	927080 150
Support leg Height 800 mm	927000 800