

Garant GRIDLINE

**Support leg with castors, Height: 950mm****Order data**

Order number	927006 950
GTIN	4062406107826
Item class	9GG

**Description****Version:**

Of steel hollow section, 50 mm wide with cross bracing and mounting for height adjustment at 25 mm intervals. Feet with plastic pads, do not damage the floor. With cable slots - for simple and professional routing of media cables / power cables.

**Supplied with:**

Support leg No. 927000, set of braked castors No. 927202 size 2.

**Colour:**

Light grey RAL 7035, **powder-coated**.

**Note:**

Support legs without rear panel or cupboards require stabilising plates No. 927122 for stiffening. The height is to the underside of the worktop.

Pre-assembled workbenches must be secured against tipping.

**Technical description**

suitable for worktop depth	750 mm
Width	50 mm
Depth	700 mm

Height	950 mm
Design version	Steel hollow section construction
Material thickness	1.5 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Support leg

---

## Accessories

WheelsSet of 2 pieces Type 2	927202 2
Support leg Height 800 mm	927000 800