

Garant GRIDLINE

**Support leg including manual height adjustment, Height: 900mm****Order data**

Order number	927001 900
GTIN	4062406107659
Item class	9GG

**Description****Version:**

Of steel hollow section, 50 mm wide with cross bracing and mounting for height adjustment at 25 mm intervals. Feet with plastic pads, do not damage the floor. With cable slots - for simple and professional routing of media cables / power cables.

**Height adjustment 150 mm.****Supplied with:**

Support leg with manual height adjustment No. 927080 size 150.

**Colour:**

Light grey RAL 7035, **powder-coated.**

**Note:**

Support legs without rear panel or cupboards require stabilising plates No. 927122 for stiffening. The height is to the underside of the worktop.

Pre-assembled workbenches must be secured against tipping.

**Technical description**

Depth	700 mm
Height adjustment range	900 - 1050 mm

Width	50 mm
suitable for worktop depth	750 mm
Height adjustment interval	25 mm
Design version	Steel hollow section construction
Material thickness	1.5 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Support leg

---

## Accessories

Manual height adjustment Type M10	927091 M10
Manual height adjustment Height adjustment 150 mm	927080 150
Support leg Height 900 mm	927000 900