

**GEDORE****Manual pipe bender set hydraulic****Order data**

Order number	821250
GTIN	4017981245616
Item class	63M

**Description****Version:**

For soft copper pipes to EN 1057 up to 22 mm (including those with thermal insulation), and for precision mild steel pipes to EN 10305-3 (DIN 2394) up to 18x1.5 mm. With hydraulic drive for a low applied force. Bending angles up to 90°.

**Supplied with:**

Hydraulic bending tool, 7 forming segments, 3 reaction pieces, plastic box.

Weight: 6.2 kg

for pipe outer Ø: 10; 12; 14; 15; 18; 20; 22 mm

**Technical description**

Weight	6.2 kg
Number of bending segments	7
for pipe outer Ø	10; 12; 14; 15; 18; 20; 22 mm
maximum bending angle	90 °
Packaging	Plastic case
Type of product	Bending machine

