

Garant**Polishing flap disc (felt), soft, Disc Ø: 115mm****Order data**

Order number	566976 115
GTIN	4045197721280
Item class	51M

Description**Version:**

The **felt strips** (height 20 mm) are edge-mounted on a glass fibre pad and permit great flexibility and cooling during the polishing process.

Application:

For **polishing up stainless steel and non-ferrous metals** in combination with polishing paste No. 555740.

For use at reduced working speeds (approx. 1500 rpm).

Technical description

Height of strips	20 mm
Bore Ø	22.23 mm
Shape description	flat
Disc Ø	115 mm
Degree of hardness	soft
Iron, sulphur and chlorine constituents	< 0.1 %
optimised for material	INOX

optimised for material	Non-ferrous metals
maximum circumferential speed	40 m/s
Type of product	Polishing flap disc

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
wet maximum	suitable		

Accessories

Polishing paste barUnipol® Colour BLUE	555740 BLUE
Polishing paste barUnipol® Colour WHITE	555740 WHITE