

RUNPOTEC
HR KABELZIEHSPEZIALIST
PowerRex fibreglass cable pulling rod in a plastic box, Band length: 30m

Order data

Order number	814868 30
GTIN	9120045473971
Item class	86A

Description
Version:

3 mm thick fibreglass rod **accepts pushing force** up to 5 kN yet is **highly flexible** (down to a radius of 55 mm); ideal for pulling cables into complicated runs where conduit is already laid or where there are many bends in the conduit.

Adhesive-bonded ferrule at each end with a thread for optional attachment of flexible guide tips, pulling grips or pulling eyes.

Supplied with:

Accessories securely stored in a plastic box: 1 **flexible starting head (Runpoglide)** with twist compensation and stainless steel pulling eye. 1 spring guide tip \varnothing 10 mm, 2 pulling eyes, 1 pulling grip for cable \varnothing 6 - 9 mm, 5 starting/end joints, 3 coupling joints, 1 special adhesive 3 g, 1 pull-in aid.

Tensile strength: 1.2 kN

Technical description

Tensile strength	1.2 kN
Band length	30 m
Type of product	Cable pulling tool

Accessories

Cable slip agent

814760

Power Disk

814770