

**RUNPOTEC**  
HR KABELZIEHSPEZIALIST

## Fibreglass pulling rod with a steel reel, Band length: 80m



### Order data

Order number	814882 80
GTIN	9120045473544
Item class	86A

### Description

#### Version:

**4.5 mm** thick fibreglass rod, **accepts pushing force** up to 5 kN yet is **flexible** (down to a radius of 120 mm). Adhesive-bonded ferrule at each end with a thread for optional attachment of flexible guide tips, pulling grips or pulling eyes. In a high-quality steel reel with extendable steel feet, 2 storage compartments with accessories, locking brake and **double outlet system** (quick outlet and automatic run-out brake).

#### Supplied with:

Accessories securely stored in a storage box: 1 **flexible starting head (Runpoglide)** with twist compensation and stainless steel pulling eye. 1 lead bulb with shackle, 1 roller, 2 starting/end joints, 1 coupling joint, 1 special adhesive 3 g.

### Technical description

Tensile strength	2.2 kN
Band length	80 m
Type of product	Cable pulling tool

