

Garant

eco grooving tool, neutral, Blade height h₅ / groove width w: 32/4mm


Order data

Order number	273866 32/4
GTIN	4045197722577
Item class	21W

Description
Version:

With eco cooling directly to the cutting edge and additional flank face cooling.

Application:

For deep grooves and parting off large diameters.

Suitable for:

Toolholder No. 273893; 273894; 274095; 274097 or VDI toolholder No. 319132 – 319133.

Spare part:

Blanking screw No. 279828 1.

Attention:

Please order the assembly key No. 279920 separately.

Note:

From 19.5 mm groove depth (up to groove width 3 mm) and from 24.5 mm groove depth (from groove width 4 mm) the second cutter comes into contact with the workpiece. This can lead to scoring. If necessary, use single-ended grooving inserts No. 273656 – 273670.

Technical description

Blade height h ₅	32 mm
Groove width w	4 mm
for maximum workpiece Ø	110 mm
Height h ₁	25 mm
Series	Eco
Overall length L	150 mm

Application type	neutral
Through-coolant	yes
axial grooving possible	no
Type of product	Parting-off tool

Accessories

Screw for ECO parting-off blade Type 1	279828 1
--	----------