



STEMI 508 stereo microscope with camera output, Type: 508CMAT



Order data

Order number	491846 508CMAT
GTIN	2050001785022
Item class	49B

Description

Version:

Stereo microscope for high resolution, intensely illuminated sharp focus images. Greenough design for the best image quality. **Apochromatic lenses** correct the chromatic aberration at the lens for three colours (red, green and blue) and thus enable brilliant colour images. Individually adjustable and to compensate for eye spacing and short-sightedness. Carrying handle for mobile use. Cold light stand, adjustable incident light, flat transillumination base (bright field / dark field), column with drive and 145 mm length of travel.

Segmentable K LED ring lamp – 48 LEDs in 2 rows.

With integral C-Mount camera output.

Supplied with:

Includes eyepieces No. 491832. Polarisation accessories for spotlighting and transillumination.

Optional extras:

AxioCam 491852 and 491853.

Technical description

Working distance	92 mm
Eyepiece	PL 10x

Magnification (x-times)	6.3 - 50
Zoom	8: 1
Field of vision Ø	35 mm
Power supply	Mains operated
Type of product	Stereo microscope

Accessories

Eyepieces for stereo microscopes, pair	491832
--	--------