




## Policap® abrasive cap (SiC), 80 grit, Abrasive cap Ø, -length, shape: 0713C



### Order data

Order number	553325 0713C
GTIN	4007220953730
Item class	55G

### Description

#### Version:

Compatible only for use with abrasive cap holders No. 553320. **Silicon carbide (SiC)** ideal for grinding titanium, aluminium and alloys of those metals. Cool grinding due to the use of abrasive additives.

#### Application:

The seamlessly formed abrasive caps slide on to the rubber body and are securely held in place by centrifugal force when the machine is running. **Abrasive caps can be replaced quickly and easily** (replace in direction of slots).

Grinding medium code: SiC

Abrasive cap Ø: 7 mm

Abrasive cap length: 13 mm

recommended speed: 30000 rpm

### Technical description

Abrasive cap length	13 mm
Abrasive cap Ø	7 mm
recommended speed	30000 rpm

Grinding media	Silicon carbide (SiC)
Grinding medium code	SiC
Grit	80
Product name attribute	80 grit

---

## Accessories

Abrasive cap holders Head Ø, head length, shape 0713C	553320 0713C
---	--------------