

**Policap® abrasive cap (SiC), 150 grit, Abrasive cap Ø, -length, shape: 1125L****Order data**

Order number	553326 1125L
GTIN	4007220953853
Item class	55G

**Description****Version:**

Compatible only for use with abrasive cap holders No. 553320. **Silicon carbide (SiC)** ideal for grinding titanium, aluminium and alloys of those metals. Cool grinding due to the use of abrasive additives.

**Application:**

The seamlessly formed abrasive caps slide on to the rubber body and are securely held in place by centrifugal force when the machine is running. **Abrasive caps can be replaced quickly and easily** (replace in direction of slots).

Grinding medium code: SiC

Abrasive cap Ø: 11 mm

Abrasive cap length: 25 mm

recommended speed: 20000 rpm

**Technical description**

Abrasive cap length	25 mm
recommended speed	20000 rpm
Abrasive cap Ø	11 mm

Grinding media	Silicon carbide (SiC)
Grinding medium code	SiC
Grit	150
Product name attribute	150 grit

---

## Accessories

Abrasive cap holders Head Ø, head length, shape 1125L	553320 1125L
---	--------------