



Abrasive cap holders, Head Ø, head length, shape: 1125L



Order data

Order number	553320 1125L
GTIN	4007220147290
Item class	55G

Description

Version:

The seamlessly formed abrasive caps slide on to the rubber body and are securely held in place by centrifugal force when the machine is running. **Abrasive caps can be replaced quickly and easily** (replace in direction of slots).

Slotted, resilient rubber body with steel shank.

Application:

Used mostly in tool making for finishing where access is difficult.

Suitable for :

Abrasive caps No. 553325 – 553326.

Shank Ø: 6 mm

maximum speed: 40000 rpm

Technical description

maximum speed	40000 rpm
Shank Ø	6 mm

