




Policap® abrasive cap (SiC), 80 grit, Abrasive cap Ø, -length, shape: 1125L



Order data

Order number	553325 1125L
GTIN	4007220953846
Item class	55G

Description

Version:

Compatible only for use with abrasive cap holders No. 553320. **Silicon carbide (SiC)** ideal for grinding titanium, aluminium and alloys of those metals. Cool grinding due to the use of abrasive additives.

Application:

The seamlessly formed abrasive caps slide on to the rubber body and are securely held in place by centrifugal force when the machine is running. **Abrasive caps can be replaced quickly and easily** (replace in direction of slots).

Grinding medium code: SiC

Abrasive cap Ø: 11 mm

Abrasive cap length: 25 mm

recommended speed: 20000 rpm

Technical description

Abrasive cap Ø	11 mm
recommended speed	20000 rpm
Abrasive cap length	25 mm

Grinding media	Silicon carbide (SiC)
Grinding medium code	SiC
Grit	80
Product name attribute	80 grit

Accessories

Abrasive cap holders Head Ø, head length, shape 1125L	553320 1125L
---	--------------