

**HOLEX****Abrasive flap sleeve (ZA) 40 grit coarse, Sleeve Ø×Width of sleeve: 60X30mm**

## Order data

Order number	553820 60X30
GTIN	4045197723130
Item class	52E

## Description

### Version:

**The band holder rubber body expands at high speed to hold the sander band in place.**

The full width of the band can be used, it does not slip and can be replaced quickly and easily (twist in the direction of slots when fitting/removing). Only compatible with ground sander band holders.

Densely packed around a stable core **abrasive strips** of Zirconium Aluminium Oxide (ZA) fabric. Due to the even wear of the individual abrasive strips, new abrasive fabric is constantly being exposed, thus increasing the service life and material removal rate several-fold.

### Application:

Sander bands are predominantly used for sanding down tasks which require the removal of large amounts of material – even at sharp edges.

For aggressive surface grinding work as an alternative to sander bands and flap wheels. For use exclusively in the direction of rotation of the support body. The direction of rotation is marked on the core of the sleeve.

### Suitable for:

Sander band holder No. 553600.

## Technical description

Grit	40
maximum speed	9500 min <sup>-1</sup>
Sleeve Ø	60 mm
Sleeve width	30 mm
External Ø	75 mm
Grit designation	coarse
Grinding media	Zirconium aluminium oxide
Grinding medium code	ZA
Sleeve shape	cylindrical
Type of product	Flap wheel sleeve

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
dry	suitable		

## Accessories

Abrasive sleeve holder, slit, shank Ø 6 mm Head Ø×head length 60X30 mm

553600 60X30

