



## Burr Tooth profile STEEL – coarse, Carbide, Type: D1614



### Order data

Order number	547100 D1614
GTIN	4007220003008
Item class	55F

### Description

#### Version:

**The innovative tooth geometry** permits **very high metal removal rates** combined with **smooth cutting and good guidance accuracy**. The optimised chip formation (no pointed chips) ensures good surface quality. Shank  $\varnothing$  6 mm.

#### Application:

Optimised for **use on steel and steel castings**.

Shank  $\varnothing$ : 6 mm

Shape description: ball

Head  $\varnothing$ : 16 mm

Head length  $L_1$ : 14 mm

Overall length: 54 mm

Shank  $\varnothing$ : 6 mm

### Technical description

Shape	D1614
Head length $L_1$	14 mm
Toothing grit designation	coarse
Tooth type abbreviation	STEEL
Head $\varnothing$	16 mm
Shape description	ball
Overall length	54 mm
Shank $\varnothing$	6 mm

Tool material	Carbide
Type of product	Burr