

HOLEX**Abrasive flap sleeve (ZA) 120 grit fine, Sleeve Ø×Width of sleeve: 30X30mm****Order data**

Order number	553823 30X30
GTIN	4045197723208
Item class	52E

Description**Version:**

The band holder rubber body expands at high speed to hold the sander band in place.

The full width of the band can be used, it does not slip and can be replaced quickly and easily (twist in the direction of slots when fitting/removing). Only compatible with ground sander band holders.

Densely packed around a stable core **abrasive strips** of Zirconium Aluminium Oxide (ZA) fabric. Due to the even wear of the individual abrasive strips, new abrasive fabric is constantly being exposed, thus increasing the service life and material removal rate several-fold.

Application:

Sander bands are predominantly used for sanding down tasks which require the removal of large amounts of material – even at sharp edges.

For aggressive surface grinding work as an alternative to sander bands and flap wheels. For use exclusively in the direction of rotation of the support body. The direction of rotation is marked on the core of the sleeve.

Suitable for:

Sander band holder No. 553600.

Technical description

Sleeve width	30 mm
maximum speed	19100 min ⁻¹
Grit	120
Sleeve Ø	30 mm
External Ø	45 mm
Grit designation	fine
Grinding media	Zirconium aluminium oxide
Grinding medium code	ZA
Sleeve shape	cylindrical
Type of product	Flap wheel sleeve

User data

	Suitability	V _c	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
dry	suitable		

Accessories

Abrasive sleeve holder, slit, shank Ø 6 mm Head Ø×head length 30X30 mm

553600 30X30

