



Flat gasket sealant, 75 ml, Manufacturer ID: 58-14



Order data

Order number	083332 58-14
GTIN	2050002005259
Item class	08G

Description

Version:

These sealants replace hemp, sealing tapes, and pastes, they are resistant to gases, liquids, air, water, oils, hydrocarbons and many chemical products. **Complete surface contact** ensures a **100% seal**. Unscrewing, or correction of position during assembly can be performed using conventional tools at any time before the sealant hardens. No sealant residues to block filters and valves.

Application:

Medium-strength, flexible, for general-purpose use, good ability to bond across gaps.

Note:

Before applying sealant, clean the surfaces with general-purpose cleaner No. 083391 and No. 083392.

Technical description

Manufacturer's designation	58-14
Labelling of hazardous substances	GHS07: Exclamation mark
Functional strength to	3 - 6 h

Working life after date of manufacture	12 mo
Capacity	75 ml
Suitable for application area	Flange connection
Dynamic viscosity	28000 - 100000 mPas
Storage temperature	10 - 25 °C
Flashpoint	100 °C
minimum break-away torque	5 Nm
Suitable for material	Metal
Operating temperature range	-55 - 150 °C
Chemical basis	anaerobic methacrylate
Shape	liquid
Touch dry after	15 - 30 min
Colour	orange
Maximum gap size	0.5 mm
Strength class	medium strength
Disassembly	with special tool
Density	1.1 g/cm ³
Product name attribute	75 ml
Type of product	Sealant

Accessories

Cleaner and degreaser spray Manufacturer's product number 7061	083391 7061
Cleaner and degreaser spray Manufacturer's product number 7063	083392 7063