

**Thread sealant, 50 ml, Manufacturer ID: 58-11****Order data**

Order number	083322 58-11
GTIN	8029822048078
Item class	08G

Description**Version:**

These sealants replace hemp, sealing tapes, and pastes, they are resistant to gases, liquids, air, water, oils, hydrocarbons and many chemical products. **Complete surface contact** ensures a **100% seal**. Unscrewing, or correction of position during assembly can be performed using conventional tools at any time before the sealant hardens. No sealant residues to block filters and valves.

Application:

Medium-strength pipe and thread sealant, NSF-P1 approved, **carries no hazard labels**.

Note:

Before applying sealant, clean the threads with general-purpose cleaner No. 083391 and No. 083392.

Technical description

Functional strength to	1 - 2 h
minimum break-away torque	18 - 24 Nm
for thread size M to	M56

Manufacturer's designation	58-11
for imperial thread size	2 in
for thread types	All
Touch dry after	15 - 30 min
Dynamic viscosity	20000 - 80000 mPas
Operating temperature range	-55 - 150 °C
Suitable for application area	all screw fastenings
Capacity	50 ml
Suitable for material	Metal
Colour	yellow
Shape	liquid
Maximum gap size	0.3 mm
Storage temperature	10 - 25 °C
Chemical basis	anaerobic methacrylate
Flashpoint	100 °C
Working life after date of manufacture	12 mo
Strength class	medium strength
Disassembly	with special tool
Density	1.1 g/cm ³
Product name attribute	50 ml
Type of product	Sealant

Accessories

Cleaner and degreaser spray Manufacturer's product number 7063

083392 7063

Cleaner and degreaser spray Manufacturer's product number 7061

083391 7061