



Flat gasket sealant, 75 ml, Manufacturer ID: 28-10



Order data

Order number	083332 28-10
GTIN	2050002005242
Item class	08G

Description

Version:

These sealants replace hemp, sealing tapes, and pastes, they are resistant to gases, liquids, air, water, oils, hydrocarbons and many chemical products. **Complete surface contact** ensures a **100% seal**. Unscrewing, or correction of position during assembly can be performed using conventional tools at any time before the sealant hardens. No sealant residues to block filters and valves.

Application:

Low-strength, very flexible, can be disassembled, bonds across gaps up to 0.3 mm.

Note:

Before applying sealant, clean the surfaces with general-purpose cleaner No. 083391 and No. 083392.

Technical description

Functional strength to	3 - 6 h
Labelling of hazardous substances	GHS07: Exclamation mark
Manufacturer's designation	28-10

Characteristics	fluorescent under UV light
Characteristics	water-resistant
Characteristics	resistant to chemicals
Suitable for material	Metal
Storage temperature	10 - 25 °C
Suitable for application area	Gearbox seal
Suitable for application area	Flange connection
Shape	liquid
Flashpoint	100 °C
minimum break-away torque	4 Nm
Capacity	75 ml
Working life after date of manufacture	12 mo
Chemical basis	anaerobic methacrylate
Dynamic viscosity	17000 - 60000 mPas
Operating temperature range	-55 - 150 °C
Touch dry after	20 - 40 min
Colour	green
Maximum gap size	0.3 mm
Strength class	low strength
Disassembly	with normal tool
Density	1.1 g/cm ³
Product name attribute	75 ml
Type of product	Sealant

Accessories

Cleaner and degreaser spray Manufacturer's product number 7061

083391 7061

083392 7063

Cleaner and degreaser spray Manufacturer's product
number 7063
