



Flat gasket sealant, 250 ml, Manufacturer ID: 58-14



Order data

| | |
|--------------|---------------|
| Order number | 083334 58-14 |
| GTIN | 8029822049099 |
| Item class | 08G |

Description

Version:

These sealants replace hemp, sealing tapes, and pastes, they are resistant to gases, liquids, air, water, oils, hydrocarbons and many chemical products. **Complete surface contact** ensures a **100% seal**. Unscrewing, or correction of position during assembly can be performed using conventional tools at any time before the sealant hardens. No sealant residues to block filters and valves.

Application:

Medium-strength, flexible, for general-purpose use, good ability to bond across gaps.

Note:

Before applying sealant, clean the surfaces with general-purpose cleaner No. 083391 and No. 083392.

Technical description

| | |
|----------------------------|---------|
| Functional strength to | 3 - 6 h |
| Manufacturer's designation | 58-14 |
| Suitable for material | Metal |

| | |
|--|------------------------|
| Storage temperature | 10 - 25 °C |
| Operating temperature range | -55 - 150 °C |
| Suitable for application area | Flange connection |
| Chemical basis | anaerobic methacrylate |
| Dynamic viscosity | 28000 - 100000 mPas |
| Capacity | 250 ml |
| Flashpoint | 100 °C |
| Working life after date of manufacture | 12 mo |
| Shape | liquid |
| minimum break-away torque | 5 Nm |
| Touch dry after | 15 - 30 min |
| Colour | orange |
| Maximum gap size | 0.5 mm |
| Disassembly | with special tool |
| Strength class | medium strength |
| Density | 1.1 g/cm ³ |
| Product name attribute | 250 ml |
| Type of product | Sealant |

Accessories

| | |
|--|-------------|
| Cleaner and degreaser spray Manufacturer's product number 7061 | 083391 7061 |
| Cleaner and degreaser spray Manufacturer's product number 7063 | 083392 7063 |