



## Flat gasket sealant, 250 ml, Manufacturer ID: 28-10



### Order data

Order number	083334 28-10
GTIN	8029822009093
Item class	08G

### Description

#### Version:

These sealants replace hemp, sealing tapes, and pastes, they are resistant to gases, liquids, air, water, oils, hydrocarbons and many chemical products. **Complete surface contact** ensures a **100% seal**. Unscrewing, or correction of position during assembly can be performed using conventional tools at any time before the sealant hardens. No sealant residues to block filters and valves.

#### Application:

Low-strength, very flexible, can be disassembled, bonds across gaps up to 0.3 mm.

#### Note:

Before applying sealant, clean the surfaces with general-purpose cleaner No. 083391 and No. 083392.

### Technical description

Labelling of hazardous substances	GHS07: Exclamation mark
Functional strength to	3 - 6 h
Manufacturer's designation	28-10

minimum break-away torque	4 Nm
Suitable for application area	Flange connection
Suitable for application area	Gearbox seal
Shape	liquid
Operating temperature range	-55 - 150 °C
Capacity	250 ml
Working life after date of manufacture	12 mo
Dynamic viscosity	17000 - 60000 mPas
Chemical basis	anaerobic methacrylate
Suitable for material	Metal
Storage temperature	10 - 25 °C
Characteristics	resistant to chemicals
Characteristics	fluorescent under UV light
Characteristics	water-resistant
Flashpoint	100 °C
Touch dry after	20 - 40 min
Colour	green
Maximum gap size	0.3 mm
Disassembly	with normal tool
Strength class	low strength
Density	1.1 g/cm <sup>3</sup>
Product name attribute	250 ml
Type of product	Sealant

## Accessories

Cleaner and degreaser spray Manufacturer's product number 7063

083392 7063

083391 7061

Cleaner and degreaser spray Manufacturer's product  
number 7061

---