

Garant GRIDLINE

**Recessed support leg including manual height adjustment, Support leg height: 900mm****Order data**

Order number	927042 900
GTIN	4062406107871
Item class	9GG

**Description****Version:**

Of steel hollow section, 50 mm wide with cross bracing and mounting for height adjustment at 25 mm intervals. Feet with plastic pads, do not damage the floor. With cable slots - for simple and professional routing of media cables / power cables.

**Colour:**

Light grey RAL 7035, **powder-coated**.

**Note:**

Support legs without rear panel or cupboards require stabilising plates No. 927122 for stiffening. Recessed support legs cannot be converted into mobile support legs. Pre-assembled workbenches must be secured against tipping.

**Technical description**

Height adjustment range	900 - 1050 mm
Width	50 mm
suitable for worktop depth	750 mm
Depth	475 mm

Design version	Steel hollow section construction
Material thickness	1.5 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Support leg

---

## Accessories

Manual height adjustment Type M10	927091 M10
Recessed support leg Support leg height 900 mm	927040 900
Manual height adjustment Height adjustment 150 mm	927080 150