

Garant GRIDLINE

**Drawer casing 16G with drawers, 12×20G, Height / number of drawers: 300/3****Order data**

Order number	927300 300/3
GTIN	4062406108137
Item class	9GG

**Description****Version:**

Drawer cabinet with sturdy steel construction. **100% full extension drawers** with differential runners and 75 kg load capacity. **Aluminium handles** with labelling strips that can be exchanged and rewritten. Can be locked centrally with cylinder lock.

**Fitted with:**

Drawer front height, mm: 50, 75, 100

**Colour:**

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

**Technical description**

Drawer usable width	300 mm
Number of doors	0
Weight	30.6 kg
Drawer usable area in G	12×20
Drawer usable width in G	12
Depth	650 mm

Number of drawers	3
Width	400 mm
Drawer usable depth	500 mm
Usable height for drawers	225 mm
Drawer usable depth in G	20
Usable width	350 mm
Usable height	225 mm
Height	300 mm
Drawer front height	50 mm
Drawer front height	75 mm
Drawer front height	100 mm
Number of pull-out shelves	0
Material thickness	1 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	12x20G
Type of product	Workbench casing

## Accessories

Drawer Drawer front height 50 mm	927500 50
Drawer Drawer front height 75 mm	927500 75
Drawer Drawer front height 100 mm	927500 100
16G cabinet casing for individual configuration with drawers Height 300 mm	927412 300

Handle end caps 20 pieces Type 10

951025 10

Lock plate for GridLine Type KO21

914227 KO21