

Garant GRIDLINE

Drawer casing 16G with drawers, 12×20G, Height / number of drawers: 300/2



Order data

Order number	927300 300/2
GTIN	4062406108120
Item class	9GG

Description

Version:

Drawer cabinet with sturdy steel construction. **100% full extension drawers** with differential runners and 75 kg load capacity. **Aluminium handles** with labelling strips that can be exchanged and rewritten. Can be locked centrally with cylinder lock.

Fitted with:

Drawer front height, mm: 75#150

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Weight	24.7 kg
Height	300 mm
Depth	650 mm
Number of doors	0
Drawer front height	75 mm
Drawer front height	150 mm

Width	400 mm
Usable height for drawers	225 mm
Drawer usable width	300 mm
Usable height	225 mm
Drawer usable depth	500 mm
Number of drawers	2
Drawer usable area in G	12×20
Usable width	350 mm
Drawer usable width in G	12
Drawer usable depth in G	20
Number of pull-out shelves	0
Material thickness	1 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	12×20G
Type of product	Workbench casing

Accessories

Drawer Drawer front height 150 mm	927500 150
Drawer Drawer front height 75 mm	927500 75
16G cabinet casing for individual configuration with drawers Height 300 mm	927412 300
Lock plate for GridLine Type KO21	914227 KO21
Handle end caps 20 pieces Type 10	951025 10