

Garant GRIDLINE

## Drawer casing 16G with drawers, 12×20G, Height / number of drawers: 800/6



### Order data

|              |               |
|--------------|---------------|
| Order number | 927300 800/6  |
| GTIN         | 4062406108175 |
| Item class   | 9GG           |

### Description

#### Version:

Drawer cabinet with sturdy steel construction. **100% full extension drawers** with differential runners and 75 kg load capacity. **Aluminium handles** with labelling strips that can be exchanged and rewritten. Can be locked centrally with cylinder lock.

#### Fitted with:

Drawer front height, mm: 75, 75, 100, 100, 150, 200

#### Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

### Technical description

|                         |        |
|-------------------------|--------|
| Height                  | 800 mm |
| Depth                   | 650 mm |
| Drawer usable depth     | 500 mm |
| Usable width            | 350 mm |
| Drawer usable area in G | 12×20  |

|  |  |
|--|--|
| Drawer front height                              | 75 mm  |
| Drawer front height                              | 75 mm  |
| Drawer front height                              | 100 mm   |
| Drawer front height                              | 100 mm   |
| Drawer front height                              | 150 mm   |
| Drawer front height                              | 200 mm   |
| Drawer usable width                              | 300 mm   |
| Usable height                                    | 700 mm   |
| Drawer usable depth in G                         | 20   |
| Width  | 400 mm   |
| Weight   | 65.5 kg  |
| Drawer usable width in G                         | 12   |
| Usable height for drawers                        | 700 mm   |
| Number of doors                                  | 0  |
| Number of drawers                                | 6  |
| Number of pull-out shelves                       | 0  |
| Material thickness                               | 1 mm   |
| Drawer/pull-out shelf load capacity              | 75 kg  |
| Drawer runner extension (partial/full extension) | 100 %  |
| Height adjustment interval                       | 25 mm  |
| Cylinder lock                                    | modular barrel   |
| Colour selection                                 | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Product name attribute                           | 12×20G   |
| Type of product                                  | Workbench casing   |

## Accessories

Drawer Drawer front height 75 mm

927500 75

|  |             |
|--|-------------|
| Drawer Drawer front height 150 mm  | 927500 150  |
| Drawer Drawer front height 200 mm  | 927500 200  |
| Drawer Drawer front height 100 mm  | 927500 100  |
| 16G cabinet casing for individual configuration with drawers Height 800 mm | 927412 800  |
| Handle end caps 20 pieces Type 10  | 951025 10   |
| Lock plate for GridLine Type KO21  | 914227 KO21 |