

Garant GRIDLINE

Drawer casing 16G with drawers, 12×20G, Height / number of drawers: 400/3



Order data

Order number	927300 400/3
GTIN	4062406108144
Item class	9GG

Description

Version:

Drawer cabinet with sturdy steel construction. **100% full extension drawers** with differential runners and 75 kg load capacity. **Aluminium handles** with labelling strips that can be exchanged and rewritten. Can be locked centrally with cylinder lock.

Fitted with:

Drawer front height, mm: 75, 100, 150

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Usable height for drawers	325 mm
Number of doors	0
Drawer usable depth in G	20
Usable width	350 mm
Weight	34.1 kg

Drawer usable depth	500 mm
Drawer front height	75 mm
Drawer front height	100 mm
Drawer front height	150 mm
Number of drawers	3
Height	400 mm
Width	400 mm
Drawer usable area in G	12×20
Usable height	325 mm
Drawer usable width	300 mm
Depth	650 mm
Drawer usable width in G	12
Number of pull-out shelves	0
Material thickness	1 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	12×20G
Type of product	Workbench casing

Accessories

Drawer Drawer front height 100 mm	927500 100
Drawer Drawer front height 75 mm	927500 75
Drawer Drawer front height 150 mm	927500 150
	927412 400

16G cabinet casing for individual configuration with
drawers Height 400 mm

Handle end caps 20 pieces Type 10

951025 10

Lock plate for GridLine Type KO21

914227 KO21