

Garant GRIDLINE

Casing 16G with door hinged on the right, Height / number of drawers: 900**Order data**

Order number	927310 900
GTIN	4062406108380
Item class	9GG

Description**Version:**

Drawer cabinet with sturdy steel construction. **100% full extension drawers** with differential runners and 75 kg load capacity. **Aluminium handles** with labelling strips that can be exchanged and rewritten. Can be locked centrally with cylinder lock.

Door hinged on the right.

Fitted with:

Door height, mm: 800

Number of height-adjustable storage shelves: 1

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Sizes 600 and 700 suitable only for Ready-to-go workbenches.

Technical description

Depth	650 mm
Width	400 mm

Number of drawers	0
Weight	32.6 kg
Usable height	800 mm
Height	900 mm
Number of doors	1
Door stop	right-hand
Door height	800 mm
Door usable height	800 mm
Usable width	350 mm
Material thickness	1 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Door opening angle	180 degrees
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Workbench casing

Accessories

Shelf carriers for shelves of workbenches Type 12	927094 12
Fixed shelf, galvanised Type 1	927515 1
Slide handle for GridLine Type KO12	914226 KO12