

Garant GRIDLINE

**Casing 16G with door hinged on the right / drawers, 12×20G, Height / number of drawers: 800/2****Order data**

Order number	927305 800/2
GTIN	4062406108328
Item class	9GG

**Description****Version:**

Drawer cabinet with sturdy steel construction. **100% full extension drawers** with differential runners and 75 kg load capacity. **Aluminium handles** with labelling strips that can be exchanged and rewritten. Can be locked centrally with cylinder lock.

Door hinged on the right.

**Fitted with:**

Drawer front height, mm: 75#75

Door height, mm: 525

Number of height-adjustable storage shelves: 1

**Colour:**

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

**Note:**

Sizes 600 and 700 suitable only for Ready-to-go workbenches.

**Technical description**

Door stop	right-hand
-----------	------------

Number of drawers	2
Usable height for drawers	150 mm
Drawer front height	75 mm
Drawer front height	75 mm
Number of doors	1
Depth	650 mm
Usable width	350 mm
Door height	525 mm
Drawer usable area in G	12×20
Drawer usable depth	500 mm
Door usable height	525 mm
Height	800 mm
Drawer usable width in G	12
Drawer usable width	300 mm
Drawer usable depth in G	20
Width	400 mm
Weight	41.3 kg
Material thickness	1 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Door opening angle	180 degrees
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	12×20G
Type of product	Workbench casing

## Accessories

Drawer Drawer front height 75 mm	927500 75
Slide handle for GridLine Type KO12	914226 KO12
Casing 16G with door hinged on the right, for individual configuration with drawers Height / door height 800/525 mm	927420 800/525
Handle end caps 20 pieces Type 10	951025 10
Lock plate for GridLine Type KO21	914227 KO21