

Garant GRIDLINE

**Drawer casing, 16G mobile, 12×20G, Casing height mm / number of drawers:
400/4****Order data**

Order number	927315 400/4
GTIN	4062406108397
Item class	9GG

Description**Version:**

Drawer cabinet with sturdy steel construction. **100% full extension drawers** with differential runners and 75 kg load capacity. **Aluminium handles** with labelling strips that can be exchanged and rewritten.

With black ABS plastic shelf and 2-component Haptoprene® push handles. With 2 each ball-bearing fixed wheels and castors, (castors with brakes for the wheels and the castor heads) Ø 125 mm, with treadless polyurethane tyres, minimum rolling resistance, low noise and fibre shields. Drawers with **individual drawer release system** prevents the opening of drawers during transport. Centrally lockable with a cylinder lock.

Fitted with:

Drawer front height, mm: 75, 75, 75, 100

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Do not slide these under workstations with electric height adjustment No. 920301 – 920316.

Technical description

Anti-roll lip version	on 4 sides
Number of drawers	4
Drawer/pull-out shelf load capacity	75 kg
Wheel Ø	125 mm
Drawer runner extension (partial/full extension)	100 %
Treadless tyres	yes
Drawer usable depth	500 mm
Electronic locking system can be retrofitted	yes
Weight	50.1 kg
Usable height	325 mm
ComfortClose	no
Height	600 mm
Drawer usable width	300 mm
Storage	yes
Depth	740 mm
Number of doors	0
with anti-roll lip	yes
maximum load capacity	600 kg
Number of fixed wheels without parking brake	2
Number of castors with parking brake	2
Width	420 mm
Material of wheel	Treadless polyurethane tyres
Drawer body height	400 mm
Drawer body width	400 mm
Drawer body usable height	325 mm
Drawer body depth	650 mm
Drawer usable depth in G	20
Drawer usable area in G	12×20
Drawer usable width in G	12

Individual drawer release system	One-hand
Version	wheeled
Version	with drawers
Casing open at the top	no
Usable height for drawers	325 mm
Number of pull-out shelves	0
Material thickness	1 mm
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	12x20G
Type of product	Workshop mobile drawer unit

Accessories

One-hand individual drawer release system Drawer usable width in G 12	951020 12
Drawer with one-handed individual drawer release system Drawer front height 100 mm	927505 100
Drawer with one-handed individual drawer release system Drawer front height 75 mm	927505 75
16G cabinet casing, mobile, for individual configuration with drawers Height of the housing 400 mm	927430 400
Lock plate for GridLine Type KO21	914227 KO21