

Garant GRIDLINE

**Drawer casing, 16G mobile, 12×20G, Casing height mm / number of drawers:  
500/3****Order data**

Order number	927315 500/3
GTIN	4062406108403
Item class	9GG

**Description****Version:**

Drawer cabinet with sturdy steel construction. **100% full extension drawers** with differential runners and 75 kg load capacity. **Aluminium handles** with labelling strips that can be exchanged and rewritten.

With black ABS plastic shelf and 2-component Haptoprene® push handles. With 2 each ball-bearing fixed wheels and castors, (castors with brakes for the wheels and the castor heads) Ø 125 mm, with treadless polyurethane tyres, minimum rolling resistance, low noise and fibre shields. Drawers with **individual drawer release system** prevents the opening of drawers during transport. Centrally lockable with a cylinder lock.

**Fitted with:**

Drawer front height, mm: 100, 125, 200

**Colour:**

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

**Note:**

Do not slide these under workstations with electric height adjustment No. 920301 – 920316.

**Technical description**

Drawer/pull-out shelf load capacity	75 kg
Number of fixed wheels without parking brake	2
with anti-roll lip	yes
Height	700 mm
Drawer runner extension (partial/full extension)	100 %
Storage	yes
Number of doors	0
Number of drawers	3
maximum load capacity	600 kg
Number of castors with parking brake	2
Depth	740 mm
Material of wheel	Treadless polyurethane tyres
Treadless tyres	yes
Weight	47.6 kg
Usable height	425 mm
Drawer usable width	300 mm
Drawer usable depth	500 mm
ComfortClose	no
Anti-roll lip version	4-sided
Wheel Ø	125 mm
Width	420 mm
Electronic locking system can be retrofitted	yes
Drawer body height	500 mm
Drawer body depth	650 mm
Drawer body width	400 mm
Drawer body usable height	425 mm
Drawer usable width in G	12
Drawer usable depth in G	20
Drawer usable area in G	12×20

Individual drawer release system	One-hand
Version	wheeled
Version	with drawers
Casing open at the top	no
Usable height for drawers	425 mm
Number of pull-out shelves	0
Material thickness	1 mm
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	12x20G
Type of product	Workshop mobile drawer unit

## Accessories

Drawer with one-handed individual drawer release system Drawer front height 125 mm	927505 125
One-hand individual drawer release system Drawer usable width in G 12	951020 12
Drawer with one-handed individual drawer release system Drawer front height 100 mm	927505 100
Drawer with one-handed individual drawer release system Drawer front height 200 mm	927505 200
16G cabinet casing, mobile, for individual configuration with drawers Height of the housing 500 mm	927430 500
Lock plate for GridLine Type KO21	914227 KO21