

Garant GRIDLINE

## Drawer casing, 16G mobile, 12×20G, Casing height mm / number of drawers: 500/5



### Order data

|              |               |
|--------------|---------------|
| Order number | 927315 500/5  |
| GTIN         | 4062406108427 |
| Item class   | 9GG           |

### Description

#### Version:

Drawer cabinet with sturdy steel construction. **100% full extension drawers** with differential runners and 75 kg load capacity. **Aluminium handles** with labelling strips that can be exchanged and rewritten.

With black ABS plastic shelf and 2-component Haptoprene® push handles. With 2 each ball-bearing fixed wheels and castors, (castors with brakes for the wheels and the castor heads) Ø 125 mm, with treadless polyurethane tyres, minimum rolling resistance, low noise and fibre shields. Drawers with **individual drawer release system** prevents the opening of drawers during transport. Centrally lockable with a cylinder lock.

#### Fitted with:

Drawer front height, mm: 75, 75, 75, 75, 125

#### Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

#### Note:

Do not slide these under workstations with electric height adjustment No. 920301 – 920316.

### Technical description

|  |                              |
|--|------------------------------|
| Drawer usable depth                              | 500 mm                       |
| Wheel Ø  | 125 mm                       |
| Number of drawers                                | 5                            |
| Treadless tyres                                  | yes                          |
| Width  | 420 mm                       |
| Anti-roll lip version                            | 4-sided                      |
| Number of fixed wheels without parking brake     | 2                            |
| Usable height                                    | 425 mm                       |
| Weight   | 59.6 kg                      |
| Drawer runner extension (partial/full extension) | 100 %                        |
| ComfortClose                                     | no                           |
| Storage  | yes                          |
| Drawer/pull-out shelf load capacity              | 75 kg                        |
| Material of wheel                                | Treadless polyurethane tyres |
| with anti-roll lip                               | yes                          |
| Number of castors with parking brake             | 2                            |
| Height   | 700 mm                       |
| Depth  | 740 mm                       |
| Drawer usable width                              | 300 mm                       |
| Electronic locking system can be retrofitted     | yes                          |
| maximum load capacity                            | 600 kg                       |
| Number of doors                                  | 0                            |
| Drawer body depth                                | 650 mm                       |
| Drawer body width                                | 400 mm                       |
| Drawer body height                               | 500 mm                       |
| Drawer body usable height                        | 425 mm                       |
| Drawer usable width in G                         | 12                           |
| Drawer usable depth in G                         | 20                           |
| Drawer usable area in G                          | 12×20                        |

|                                  |  |
|----------------------------------|--|
| Individual drawer release system | One-hand   |
| Version                          | wheeled  |
| Version                          | with drawers   |
| Number of pull-out shelves       | 0  |
| Usable height for drawers        | 425 mm   |
| Casing open at the top           | no   |
| Material thickness               | 1 mm   |
| Height adjustment interval       | 25 mm  |
| Cylinder lock                    | modular barrel   |
| Colour selection                 | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Product name attribute           | 12x20G   |
| Type of product                  | Workshop mobile drawer unit                                    |

## Accessories

|  |             |
|--|-------------|
| One-hand individual drawer release system Drawer usable width in G 12                              | 951020 12   |
| Drawer with one-handed individual drawer release system Drawer front height 125 mm                 | 927505 125  |
| Drawer with one-handed individual drawer release system Drawer front height 75 mm                  | 927505 75   |
| 16G cabinet casing, mobile, for individual configuration with drawers Height of the housing 500 mm | 927430 500  |
| Lock plate for GridLine Type KO21  | 914227 KO21 |