

Garant GRIDLINE

16G cabinet casing complete with swing away and height adjustment unit and vice, Height: 700mm**Order data**

Order number	927320 700
GTIN	4062406108441
Item class	9GG

Description**Version:**

16G cabinet casing in sturdy steel construction. Door can be locked with a **cylinder lock**. Drawer not lockable.

With GARANT swing away and height adjustment unit No. 967565 size 120 and vice No. 967100 size 120.

Fitted with:

Door height, mm: 625

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated**. **Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Depth	650 mm
Height	700 mm
Width	400 mm
Weight	46.6 kg

Usable width	280 mm
Usable height	670 mm
Usable depth	600 mm
Material thickness	1 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Support leg

Accessories

Swing away mounting and height adjuster with vice Vice jaw width 120 mm	967565 120
Slide handle for GridLine Type KO12	914226 KO12
Bench vice Jaw width 120 mm	967100 120