


eco grooving toolholder, Blade height h₅ / Shank height h: 26/20 mm

Order data

Order number	273868 26/20
GTIN	4045197722928
Item class	21W

Description
Note:

Coolant transfer only in conjunction with GARANT eco-system toolholders No. 319001 – 319886.

Through-coolant: true

Clamping claw: 279991

Clamping screw: 279990

Blade height h₅: 26 mm

h₄: 20 mm

h₂: 11 mm

h₃: 49 mm

b: 20 mm

b₃: 43 mm

Technical description

Shank height h	20 mm
Shoulder length b	20 mm
Shank width b ₃	43 mm
h ₄	20 mm
h ₃	49 mm

h ₂	11 mm
Overall length L _{tot}	78 mm
Through-coolant	yes
Clamping claw	279840 2
Clamping screw	279815 14

Accessories

Clamping claw	279991
Clamping screw	279990
Torx® bit, shank E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cN·m	659906 500