

Garant GRIDLINE

16G cabinet casing suitable for swing away and height adjustment unit and vice, Height: 600mm**Order data**

Order number	927321 600
GTIN	4062406108472
Item class	9GG

Description**Version:**

16G cabinet casing in sturdy steel construction. Door can be locked with a **cylinder lock**. Drawer not lockable.

Suitable for GARANT swing away and height adjustment unit No. 967565 size 120 and vice No. 967100 size 120 (not included).

Fitted with:

Door height, mm: 525

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated**. **Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Weight	23.9 kg
Width	400 mm
Height	600 mm
Depth	650 mm

Usable depth	600 mm
Usable width	280 mm
Usable height	570 mm
Material thickness	1 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Support leg

Accessories

Swing away mounting and height adjuster with vice Vice jaw width 120 mm	967565 120
Slide handle for GridLine Type KO12	914226 KO12
Bench vice Jaw width 120 mm	967100 120