

Garant GRIDLINE

**Energy casing with hose reel, Height: 700mm****Order data**

Order number	927328 700
GTIN	4062406108595
Item class	9GG

**Description****Version:**

16G cabinet casing in sturdy steel construction.

Equipped with 2 × No. 928470 size DE250V/1, cable reel / hose reel, securely bolted to the casing base. Length on the cable reel 10 m. Length on the hose reel 10 m.

Connection NW 7.2 male coupling and quick-release coupling. With quick-lock coupling. Max. pressure 12 bar.

**Fitted with:**

Module No. 928470: 2 × size DE250V/1; 1 × size 0/1

**Colour:**

Body and modules RAL 7035 light grey, front RAL 7016 anthracite **powder-coated**.

**Note:**

Further individual configuration options with modules No. 928470. Keep within the maximum permissible number of modules.

**Technical description**

Depth	650 mm
Width	400 mm

Height	700 mm
Weight	28.2 kg
Power supply	Mains operated
Nominal voltage	250 V
Plug type, input	GST plug-in system
Number of sockets type F	2
Socket type	F
Material thickness	1 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Power module

## Accessories

Module for energy and media Module type 0/1	928470 0/1
Module for energy and media Module type DE250V/1	928470 DE250V/1