

Garant GRIDLINE

Energy casing with hose reel, Height: 900mm



Order data

Order number	927328 900
GTIN	4062406108618
Item class	9GG

Description

Version:

16G cabinet casing in sturdy steel construction.

Equipped with 2 × No. 928470 size DE250V/1, cable reel / hose reel, securely bolted to the casing base. Length on the cable reel 10 m. Length on the hose reel 10 m.

Connection NW 7.2 male coupling and quick-release coupling. With quick-lock coupling. Max. pressure 12 bar. With additional blank fascia for optional fitting of 3 further modules.

Fitted with:

Module No. 928470: 2 × size DE250V/1; 1 × size 0/1 and 0/3

Colour:

Body and modules RAL 7035 light grey, front RAL 7016 anthracite **powder-coated**.

Note:

Further individual configuration options with modules No. 928470. Keep within the maximum permissible number of modules.

Technical description

Depth	650 mm
Height	900 mm

Weight	32.4 kg
Width	400 mm
Power supply	Mains operated
Plug type, input	GST plug-in system
Nominal voltage	250 V
Number of sockets type F	2
Socket type	F
Material thickness	1 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Power module

Accessories

Module for energy and media Module type 0/1	928470 0/1
Module for energy and media Module type DE250V/1	928470 DE250V/1